

6

5


4

3


2

1

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	12/06/2023	BZHANG	GUTTADAURO



2X RJ45 SHIELDED PLUG
GOLD PLATED CONTACTS



PART NUMBER	LENGTH METERS[FEET]
TRD795GRN-05M	0.5[1.64]
TRD795GRN-1M	1.0[3.28]
TRD795GRN-2M	2.0[6.56]
TRD795GRN-3M	3.0[9.84]
TRD795GRN-5M	5.0[16.41]
TRD795GRN-7.5M	7.5[24.61]
TRD795GRN-10M	10.0[32.81]
TRD795GRN-15M	15.0[49.21]

- NOTES:
- 1.LENGTHS OVER 10 METERS (32.8 FT) ARE CHANNEL RATED.
 - 2.PLUG CONFORMS TO TIA-1096.
 - 3.CABLE ASSEMBLY TO BE TESTED FOR CONTINUITY.
 - 4.CABLE ASSEMBLY TO BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

<small>UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS</small> TOLERANCES: .X = ±.2 [5] FRACTIONS ± 1/32 .XX = ±.02 [0.5] ANGLES ± 1° .XXX = ±.005 [0.13]	 an INFINIT@ brand Website: www.L-com.com Phone: 1.800.341.5266 1.978.682.6936	 <small>INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5</small> SCALE: NONE SHEET: 1 OF 1
DESCRIPTION: CA,CAT7 S/FTP RJ45 TO RJ45 PVC JKT,GRN		
SIZE: A	CAGE CODE: 43321	DRAWN BY: BZHANG
ITEM NO.: TRD795GRN		REV: A

6

5

4

3

2

1