





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS | | | |
|-----------|--|------------|---------------|
| REV | DESCRIPTION | DATE | APPROVED |
| E | ECN 10806: ADD LSZH CABLE CHARACTERISTICS TO DWG, NEW FORMAT | 11/25/2020 | D.Guiffadauro |
| | | | |
| | | | |




LSZH CABLE CHARACTERISTICS: 
 FLAME RATING: IEC 60332-1
 CORROSIVE GAS: IEC 60754
 SMOKE EMISSION: IEC 61034

- NOTES:**
1. PLUG CONFORMS TO TIA-1096
 2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

| | | | | | | | |
|--|--|-------------------------------|---|-----------------------------|---------------------------|-------------------------------|------------------|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS .XX = ± .02 [5] ± 1/32 .XXX = ± .005 [13] ANGLES ± 1° THIRD-ANGLE PROJECTION  | APPROVALS | DATE |  50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936 | | | | |
| | DRAWN BY D.FRISIELLO | 1/27/12 | | CATEGORY TELECOM/MODULAR | | | |
| | CHECKED BY J.RUST | 1/27/12 | PRODUCT DESCRIPTION C5E LSZ UTP UP-UP | | | | |
| | APPROVED BY D.GALLAGHER | 1/27/12 | <table border="1"> <tr> <td>SIZE A</td> <td>CAGE CODE 43321</td> <td>ITEM NO. TRD815ZRA5</td> <td>REV. E</td> </tr> </table> | SIZE A | CAGE CODE 43321 | ITEM NO. TRD815ZRA5 | REV. E |
| SIZE A | CAGE CODE 43321 | ITEM NO. TRD815ZRA5 | REV. E | | | | |
| | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY | COLOR VARIATIONS MAY OCCUR | SCALE: NONE CAD FILE: TRD815ZRA5.SLDDRW SHEET 1 OF 2 | | | | |

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| PART NUMBER | COLOR | LENGTH FEET [METERS] | PART NUMBER | COLOR | LENGTH FEET [METERS] | PART NUMBER | COLOR | LENGTH FEET [METERS] |
|------------------|-------|----------------------|-----------------|-------|----------------------|------------------|-------|----------------------|
| TRD815ZRA5BLK-1 | BLACK | 1.0 [0.30] | TRD815ZRA5RD-1 | RED | 1.0 [0.30] | TRD815ZRA5GRY-1 | GRAY | 1.0 [0.30] |
| TRD815ZRA5BLK-2 | BLACK | 2.0 [0.61] | TRD815ZRA5RD-2 | RED | 2.0 [0.61] | TRD815ZRA5GRY-2 | GRAY | 2.0 [0.61] |
| TRD815ZRA5BLK-3 | BLACK | 3.0 [0.91] | TRD815ZRA5RD-3 | RED | 3.0 [0.91] | TRD815ZRA5GRY-3 | GRAY | 3.0 [0.91] |
| TRD815ZRA5BLK-5 | BLACK | 5.0 [1.52] | TRD815ZRA5RD-5 | RED | 5.0 [1.52] | TRD815ZRA5GRY-5 | GRAY | 5.0 [1.52] |
| TRD815ZRA5BLK-7 | BLACK | 7.0 [2.13] | TRD815ZRA5RD-7 | RED | 7.0 [2.13] | TRD815ZRA5GRY-7 | GRAY | 7.0 [2.13] |
| TRD815ZRA5BLK-10 | BLACK | 10.0 [3.05] | TRD815ZRA5RD-10 | RED | 10.0 [3.05] | TRD815ZRA5GRY-10 | GRAY | 10.0 [3.05] |
| TRD815ZRA5BLK-15 | BLACK | 15.0 [4.57] | TRD815ZRA5RD-15 | RED | 15.0 [4.57] | TRD815ZRA5GRY-15 | GRAY | 15.0 [4.57] |
| TRD815ZRA5BLK-20 | BLACK | 20.0 [6.10] | TRD815ZRA5RD-20 | RED | 20.0 [6.10] | TRD815ZRA5GRY-20 | GRAY | 20.0 [6.10] |
| TRD815ZRA5BLK-25 | BLACK | 25.0 [7.62] | TRD815ZRA5RD-25 | RED | 25.0 [7.62] | TRD815ZRA5GRY-25 | GRAY | 25.0 [7.62] |
| TRD815ZRA5BLK-30 | BLACK | 30.0 [9.14] | TRD815ZRA5RD-30 | RED | 30.0 [9.14] | TRD815ZRA5GRY-30 | GRAY | 30.0 [9.14] |

| | | | |
|---|---------------------------|---|------------------|
|  | | 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936 | |
| CATEGORY <p style="text-align: center;">TELECOM/MODULAR</p> | | | |
| PRODUCT DESCRIPTION <p style="text-align: center;">C5E LSZ UTP UP-UP</p> | | | |
| SIZE A | CAGE CODE 43321 | ITEM NO. TRD815ZRA5 | REV. E |
| SCALE: NONE | | CAD FILE: TRD815ZRA5.SLDDRW | |
| | | | SHEET 2 OF 2 |