



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 10806: ADD LSZH CABLE CHARACTERISTICS TO DWG, NEW FORMAT	11/25/2020	D.Guhtadauro



LSZH CABLE CHARACTERISTICS:


FLAME RATING: IEC 60332-1
CORROSIVE GAS: IEC 60754
SMOKE EMISSION: IEC 61034

- NOTES:**
1. PLUG CONFORMS TO TIA-1096
 2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE	 an INFINITI® brand	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	OVERALL CABLE LENGTH TOLERANCE:	DRAWN BY D.FRISIELLO		1/26/12	CATEGORY TELECOM/MODULAR
<12 [305] ≤+1 [25] / -0 >12 [305] ≤+6 [1524] = +2 [51] / -0 >60 [1524] ≤+120 [3048] = +4 [102] / -0 >120 [3048] ≤+300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0	CHECKED BY J.RUST	1/26/12	PRODUCT DESCRIPTION C5E LSZH UTP DWN-DWN		
ALL OTHER DIMENSIONAL TOLERANCES:	APPROVED BY D.GALLAGHER	1/26/12	SIZE A	CAGE CODE 43321	ITEM NO. TRD815ZRA3
THIRD-ANGLE PROJECTION	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SCALE: NONE	CAD FILE: TRD815ZRA3.SLDDRW	SHEET 1 OF 2
.X ± .2 [5] FRACTIONS .XX ± .02 [5] ± 1/32 .XXX ± .005 [13] ANGLES ± 1°	COLOR VARIATIONS MAY OCCUR		REV. E		

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]
TRD815ZRA3BLK-1	BLACK	1.0 [0.30]	TRD815ZRA3RD-1	RED	1.0 [0.30]	TRD815ZRA3GRY-1	GRAY	1.0 [0.30]
TRD815ZRA3BLK-2	BLACK	2.0 [0.61]	TRD815ZRA3RD-2	RED	2.0 [0.61]	TRD815ZRA3GRY-2	GRAY	2.0 [0.61]
TRD815ZRA3BLK-3	BLACK	3.0 [0.91]	TRD815ZRA3RD-3	RED	3.0 [0.91]	TRD815ZRA3GRY-3	GRAY	3.0 [0.91]
TRD815ZRA3BLK-5	BLACK	5.0 [1.52]	TRD815ZRA3RD-5	RED	5.0 [1.52]	TRD815ZRA3GRY-5	GRAY	5.0 [1.52]
TRD815ZRA3BLK-7	BLACK	7.0 [2.13]	TRD815ZRA3RD-7	RED	7.0 [2.13]	TRD815ZRA3GRY-7	GRAY	7.0 [2.13]
TRD815ZRA3BLK-10	BLACK	10.0 [3.05]	TRD815ZRA3RD-10	RED	10.0 [3.05]	TRD815ZRA3GRY-10	GRAY	10.0 [3.05]
TRD815ZRA3BLK-15	BLACK	15.0 [4.57]	TRD815ZRA3RD-15	RED	15.0 [4.57]	TRD815ZRA3GRY-15	GRAY	15.0 [4.57]
TRD815ZRA3BLK-20	BLACK	20.0 [6.10]	TRD815ZRA3RD-20	RED	20.0 [6.10]	TRD815ZRA3GRY-20	GRAY	20.0 [6.10]
TRD815ZRA3BLK-25	BLACK	25.0 [7.62]	TRD815ZRA3RD-25	RED	25.0 [7.62]	TRD815ZRA3GRY-25	GRAY	25.0 [7.62]
TRD815ZRA3BLK-30	BLACK	30.0 [9.14]	TRD815ZRA3RD-30	RED	30.0 [9.14]	TRD815ZRA3GRY-30	GRAY	30.0 [9.14]


 100 High Street, West Mill,
 Andover, MA 01845 USA.
 1.800.341.5266
 1.978.682.6936

CATEGORY: TELECOM/MODULAR

PRODUCT DESCRIPTION: C5E LSZ UTP DWN-DWN

SIZE A	CAGE CODE 43321	ITEM NO. TRD815ZRA3	REV. E
------------------	---------------------------	------------------------	------------------

SCALE: NONE | CAD FILE: TRD815ZRA3.SLDDRW | SHEET 2 OF 2