


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 10806:ADD LSZH CABLE CHARACTERISTICS TO DWG, NEW FORMAT	11/25/2020	D.Guiffadauro



P1  
RJ45 MODULAR  
UNSHIELDED PLUG  
GOLD PLATED CONTACTS  
(8P8C)

P2  
RJ45 MODULAR  
UNSHIELDED PLUG  
GOLD PLATED CONTACTS  
(8P8C)

**WIRING MAP**




**LSZH CABLE CHARACTERISTICS:**   
 FLAME RATING: IEC 60332-1  
 CORROSIVE GAS: IEC 60754  
 SMOKE EMISSION: IEC 61034

- NOTES:**
1. PLUG CONFORMS TO TIA-1096
  2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
  3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]      FRACTIONS ± 1/32 .XX = ± .02 [5]      ± 1/32 .XXX = ± .005 [13]      ANGLES ± 1° THIRD-ANGLE PROJECTION 	APPROVALS DRAWN BY D.FRISIELLO 1/27/12 CHECKED BY J.RUST 1/27/12 APPROVED BY D.GALLAGHER 1/27/12	DATE 1/27/12 1/27/12 1/27/12	an INFINITI brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	CATEGORY TELECOM/MODULAR PRODUCT DESCRIPTION C5E LSZH UTP LFT-LFT	SIZE <b>A</b> CAGE CODE <b>43321</b> ITEM NO. <b>TRD815ZRA9</b>

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]
TRD815ZRA9BLK-1	BLACK	1.0 [0.30]	TRD815ZRA9RD-1	RED	1.0 [0.30]	TRD815ZRA9GRY-1	GRAY	1.0 [0.30]
TRD815ZRA9BLK-2	BLACK	2.0 [0.61]	TRD815ZRA9RD-2	RED	2.0 [0.61]	TRD815ZRA9GRY-2	GRAY	2.0 [0.61]
TRD815ZRA9BLK-3	BLACK	3.0 [0.91]	TRD815ZRA9RD-3	RED	3.0 [0.91]	TRD815ZRA9GRY-3	GRAY	3.0 [0.91]
TRD815ZRA9BLK-5	BLACK	5.0 [1.52]	TRD815ZRA9RD-5	RED	5.0 [1.52]	TRD815ZRA9GRY-5	GRAY	5.0 [1.52]
TRD815ZRA9BLK-7	BLACK	7.0 [2.13]	TRD815ZRA9RD-7	RED	7.0 [2.13]	TRD815ZRA9GRY-7	GRAY	7.0 [2.13]
TRD815ZRA9BLK-10	BLACK	10.0 [3.05]	TRD815ZRA9RD-10	RED	10.0 [3.05]	TRD815ZRA9GRY-10	GRAY	10.0 [3.05]
TRD815ZRA9BLK-15	BLACK	15.0 [4.57]	TRD815ZRA9RD-15	RED	15.0 [4.57]	TRD815ZRA9GRY-15	GRAY	15.0 [4.57]
TRD815ZRA9BLK-20	BLACK	20.0 [6.10]	TRD815ZRA9RD-20	RED	20.0 [6.10]	TRD815ZRA9GRY-20	GRAY	20.0 [6.10]
TRD815ZRA9BLK-25	BLACK	25.0 [7.62]	TRD815ZRA9RD-25	RED	25.0 [7.62]	TRD815ZRA9GRY-25	GRAY	25.0 [7.62]
TRD815ZRA9BLK-30	BLACK	30.0 [9.14]	TRD815ZRA9RD-30	RED	30.0 [9.14]	TRD815ZRA9GRY-30	GRAY	30.0 [9.14]

		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
CATEGORY			
TELECOM/MODULAR			
PRODUCT DESCRIPTION			
C5E LSZ UTP LFT-LFT			
SIZE	CAGE CODE	ITEM NO.	REV.
<b>A</b>	<b>43321</b>	TRD815ZRA9	<b>E</b>
SCALE: NONE		CAD FILE: TRD815ZRA9.SLDDRW	
			SHEET 2 OF 2