




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	2/21/14	D.GRIFFIN



SLIP-ON SNAGLESS BOOT
LSZH, COLOR: BLACK

FOUR TWISTED PAIRS, CATEGORY 5E
26 AWG STRANDED COPPER WITH
ALUMINUM/POLYESTER SHIELDING AND DRAIN WIRE
PVC JACKET SEE SHEET 2 FOR COLOR



NOTES:


1. PLUG CONFORMS TO TIA-1096.
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 > 12 [305] ≤ 60 [1524] = +2 [51] / -0 > 60 [1524] ≤ 120 [3048] = +4 [102] / -0 > 120 [3048] ≤ 300 [7620] = +6 [152] / -0 > 300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [5.1] .XXX = ± .005 [1.3]	APPROVALS D. DESJARDIN CHECKED BY D. FRISIELLO APPROVED BY D. GALLAGHER	DATE 10/15/13 2/12/20 2/20/14	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			CATEGORY TELECOM/MODULAR
	PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
	DWG. NO. TRD845LS		SCALE: NONE	CAD FILE: TRD845LS.LDDRW
SHEET 1 OF 2			REV. A	

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC., ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]
TRD845LSBLK-1	BLACK	1.0 [0.30]	TRD845LSRED-1	RED	1.0 [0.30]
TRD845LSBLK-3	BLACK	3.0 [0.91]	TRD845LSRED-3	RED	3.0 [0.91]
TRD845LSBLK-5	BLACK	5.0 [1.52]	TRD845LSRED-5	RED	5.0 [1.52]
TRD845LSBLK-7	BLACK	7.0 [2.13]	TRD845LSRED-7	RED	7.0 [2.13]
TRD845LSBLK-10	BLACK	10.0 [3.05]	TRD845LSRED-10	RED	10.0 [3.05]
TRD845LSBLU-1	BLUE	1.0 [0.30]	TRD845LSGRY-1	GRAY	1.0 [0.30]
TRD845LSBLU-3	BLUE	3.0 [0.91]	TRD845LSGRY-3	GRAY	3.0 [0.91]
TRD845LSBLU-5	BLUE	5.0 [1.52]	TRD845LSGRY-5	GRAY	5.0 [1.52]
TRD845LSBLU-7	BLUE	7.0 [2.13]	TRD845LSGRY-7	GRAY	7.0 [2.13]
TRD845LSBLU-10	BLUE	10.0 [3.05]	TRD845LSGRY-10	GRAY	10.0 [3.05]

		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
CATEGORY			
TELECOM/MODULAR			
PRODUCT DESCRIPTION			
C5E PVC FTP 45DEG L			
SIZE	FSCM NO.	DWG. NO.	REV.
A	43321	TRD845LS	A
SCALE: NONE		CAD FILE: TRD845LS.SLDDRW	SHEET 2 OF 2