


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	6/7/17	D.FRISIELLO



*CONTACTS SHOWN CRIMPED

- NOTES:
1. PLUG KIT CONSISTS OF: PRE-INSERTED PLUG HOUSING.
 2. MATERIALS:
FRONT HOUSING PLASTIC: CLEAR POLYCARBONATE, UL 94-V0
CONTACTS: PHOSPHOR BRONZE, 50 μINCHES GOLD PLATING.
 3. CONTACTS TERMINATE STRANDED OR SOLID CONDUCTORS UP TO .037" [0.94] MAX. OUTSIDE DIAMETER OF INSULATION.
 4. TERMINATED PLUG HEIGHT: .237" [6.02] +/- .005 [0.13]
 5. COMPONENT SHALL BE PACKAGED IN BULK OF 100 PIECES PER BAG IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .XXX = ±.005 [0.13]	APPROVALS DRAWN BY D.FRISIELLO	DATE 6/1/17		50 HIGH STREET NORTH ANDOVER, MA 01845			
	CHECKED BY M.MARTINEZ	6/7/17		CATEGORY TELECOM/MODULAR			
	APPROVED BY D.GUITADAURO	6/7/17	PRODUCT DESCRIPTION PLUG, HANDSET (4P4C)	SIZE A	FSCM NO. 43321	DWG. NO. TSP3044	REV. A
	PROJECTION 	COLOR VARIATIONS MAY OCCUR	SCALE: NONE	CAD FILE: TSP3044.SLDDRW	SHEET 1 OF 1		