

78 Ohm TRS Subminiature 3-Slot Plug 1553 Connector Clamp/
Solder Attachment for 30-02003-LC, TWC-78-1



LCCN10-10030-231

Configuration

- TRS Subminiature Plug Connector
- MIL-STD-1553
- 78 Ohms
- Straight Body Geometry
- 30-02003-LC, TWC-78-1 Interface Type
- Clamp/Solder Attachment
- 1553 Design

Features

- Twinax Connectivity
- Subminiature

Applications

- Robust Design
- Ease of Use
- Use in High Shock and Vibration Environment

Description

TRS Subminiature Plug connector has a bayonet coupling design with a center contact and an intermediate cylindrical contact. TRS connectors are preferred in applications that require weight reduction, high packing density, and noise-free guarded circuits. TRS connectors can increase packing density to more than 240% compared to TRB standard connectors. The reduced size limits the maximum outer cable diameter to 0.250 inches.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		500	MHz
Insertion Loss		0.1		dB

Mechanical Specifications

Size

Length	0.77 in [19.56 mm]
Width	0.44 in [11.18 mm]
Height	0.44 in [11.18 mm]
Weight	0.03 lbs [11.34 g]

Material Specifications

Description	Material	Plating
Contact	Beryllium Copper	Gold 30 micro inches ASTM-B-488
Insulation	Teflon	
Outer Conductor	Phosphor Bronze	ASTM-B-488

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:
[78 Ohm TRS Subminiature 3-Slot Plug 1553 Connector Clamp/Solder Attachment for 30-02003-LC, TWC-78-1 LCCN10-10030-231](#)

78 Ohm TRS Subminiature 3-Slot Plug 1553 Connector Clamp/
Solder Attachment for 30-02003-LC, TWC-78-1



LCCN10-10030-231

Body	Brass	Nickel ASTM-B-733
------	-------	----------------------

Environmental Specifications

Temperature

Operating Range -55deg C to +200deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

78 Ohm TRS Subminiature 3-Slot Plug 1553 Connector Clamp/Solder Attachment for 30-02003-LC, TWC-78-1 from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components. Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 78 Ohm TRS Subminiature 3-Slot Plug 1553 Connector Clamp/Solder Attachment for 30-02003-LC, TWC-78-1 LCCN10-10030-231

URL: <https://www.l-com.com/78-ohm-trs-subminiature-3-slot-plug-1553-connector-clamp-solder-attachment-30-02003-lc-twc-78-1-lccn10-10030-231-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document. The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

L-com CAD Drawing

