

Fiber Enclosure Rack Mount 1U (1.75") 48 Port (24 Duplex) LC/APC Couplers with 48 SC/APC 0.9mm Pigtailes



LCFPP-SL01-24LCA2

Features

- 48 Port (24 Duplex) SC/APC Couplers Installed along with 48 LC/APC 0.9mm Pigtailes
- 1U (1.75") 19 Inch Rack Mount design
- Cable Management Tray designed to securely and safely hold your fiber strands
- Sliding tray design allows for easy access to your fiber connections even while installed in a standard 19 inch rack
- TIA/EIA-568-B.3 compliant

Applications

- FTTH Access Networks
- Telecommunication Networks
- CATV Networks
- Data Communications Networks
- Local Area Networks

Description

This 19 Inch Rack Mount Fiber Enclosure, the LCFPP-SL01-24LCA2, and its low profile 1U (1.75") design comes with 24 Duplex LC/APC couplers pre-installed providing 48 ports of connection. The fiber enclosure also comes with 48 LC/APC 0.9mm pigtailes. Ideal for fiber termination in your network closet, the slide out tray provides easy access to your fiber optic connections.

Size

Outer Height	1.75 in	[44.45 mm]
Outer Width	19 in	[482.6 mm]
Outer Depth	9.5 in	[241.3 mm]
Weight	8.8 lbs	[3.99 kg]
Enclosure Material	SPCC Cold Rolled Steel	
Enclosure Material Thickness	16 Gauge	
Operating Temperature	-40 to 60 deg C	

Fiber Enclosure Rack Mount 1U (1.75") 48 Port (24 Duplex) LC/APC Couplers with 48 SC/APC 0.9mm Pigtailes from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components. Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Fiber Enclosure Rack Mount 1U (1.75") 48 Port (24 Duplex) LC/APC Couplers with 48 SC/APC 0.9mm Pigtailes LCFPP-SL01-24LCA2

URL: <https://www.l-com.com/fiber-enclosure-rack-mount-1u-175-48-port-24-duplex-lc-apc-couplers-with-48-sc-apc-09mm-pigtailes-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

Fiber Enclosure Rack Mount 1U (1.75") 48 Port (24 Duplex) LC/APC Couplers with 48 SC/APC 0.9mm Pigtails

L-com CAD Drawing

