

TRB Plug Full Crimp Connector for 752BA5314 Cable



LCCN310-06031-303

Configuration

- TRB Plug Connector
- Straight Body Geometry
- Raychem 7528A5314 Interface Type
- Crimp/Solder Attachment

Electrical Specifications

| Description | Minimum | Typical | Maximum | Units |
|------------------------|---------|---------|---------|-------|
| Frequency Range | DC | | 500 | MHz |
| Operating Voltage (AC) | | | 5,000 | Vrms |

Mechanical Specifications

Size

| | |
|---------------|--------------------|
| Length | 1.60 in [40.64 mm] |
| Width | 0.50 in [12.70 mm] |
| Height | 0.50 in [12.70 mm] |
| Weight | 0.05 lbs [22.68 g] |
| Mating Cycles | 500 Cycles |

Material Specifications

| Description | Material | Plating |
|---------------|------------------|---------|
| Contact | Beryllium Copper | Gold |
| Insulation | PTFE | |
| Body | Brass | Nickel |
| Coupling Nut | Brass | Nickel |
| Washer | Brass | Nickel |
| Shrink Tubing | PVDF | |

Environmental Specifications

Temperature

| | |
|-----------------|-----------------------|
| Operating Range | -65deg C to +165deg C |
|-----------------|-----------------------|

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:
[TRB Plug Full Crimp Connector for 752BA5314 Cable LCCN310-06031-303](#)

TRB Plug Full Crimp Connector for 752BA5314 Cable



LCCN310-06031-303

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

TRB Plug Full Crimp Connector for 752BA5314 Cable from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components. Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: TRB Plug Full Crimp Connector for 752BA5314 Cable LCCN310-06031-303

URL: <https://www.l-com.com/trb-plug-full-crimp-connector-752ba5314-cable-lccn310-06031-303-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document. The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

TRB Plug Full Crimp Connector for 752BA5314 Cable

L-com CAD Drawing

