

Fiber Enclosure Rack Mount 1U (1.75") 48 Port (24 Duplex) LC/UPC Couplers with 48 LC/UPC 0.9mm Pigtaills



## LCFPP-SL01-24LC2

### Features

- 48 Port (24 Duplex) LC/UPC Couplers Installed along with 48 LC/UPC 0.9mm Pigtaills
- 1U (1.75") 19 Inch Rack Mount design
- Cable Management Tray designed to securely and safely hold your fiber strands
- Sliding tray design allows for easy access to your fiber connections even while installed in a standard 19 inch rack
- TIA/EIA-568-B.3 compliant

### Applications

- FTTH Access Networks
- Telecommunication Networks
- CATV Networks
- Data Communications Networks
- Local Area Networks

### Description

This 19 Inch Rack Mount Fiber Enclosure, the LCFPP-SL01-24LC2, and its low profile 1U (1.75") design comes with 24 Duplex LC/UPC couplers pre-installed providing 48 ports of connection. The fiber enclosure also comes with 48 LC/UPC 0.9mm pigtaills. Ideal for fiber termination in your network closet, the slide out tray provides easy access to your fiber optic connections.

### Mechanical Specifications

#### Size

Outer Height	1.75 in	[44.45 mm]
Outer Width	19 in	[482.6 mm]
Outer Depth	9.5 in	[241.3 mm]
Weight	8.8 lbs	[3.99 kg]
Enclosure Material	SPCC Cold Rolled Steel	
Enclosure Material Thickness	16 Gauge	

### Environmental Specifications

Operating Temperature	-40 to 60 deg C
-----------------------	-----------------

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:  
[Fiber Enclosure Rack Mount 1U \(1.75"\) 48 Port \(24 Duplex\) LC/UPC Couplers with 48 LC/UPC 0.9mm Pigtaills LCFPP-SL01-24LC2](#)

Fiber Enclosure Rack Mount 1U (1.75") 48 Port (24 Duplex) LC/UPC Couplers with 48 LC/UPC 0.9mm Pigtailes



## LCFPP-SL01-24LC2

Fiber Enclosure Rack Mount 1U (1.75") 48 Port (24 Duplex) LC/UPC Couplers with 48 LC/UPC 0.9mm Pigtailes from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components. Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Fiber Enclosure Rack Mount 1U (1.75") 48 Port (24 Duplex) LC/UPC Couplers with 48 LC/UPC 0.9mm Pigtailes LCFPP-SL01-24LC2

URL: <https://www.l-com.com/fiber-enclosure-rack-mount-1u-175-48-port-24-duplex-lc-upc-couplers-with-48-sc-upc-09mm-pigtails-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

