

Passive PM Dual Stage Isolator, Grade P, 1480nm, 1M 900um loose tube, FC/APC, narrow key



PPMDI-P48-191

Features

- · Polarized Maintaining
- · Dual Stage, Grade P (Premium)
- · 1M, FC /APC

Applications

- Optical Amplifier
- · Communication Networks
- · Fiber Sensors

- · Low Insertion Loss
- · High Isolation
- · Coherent Dedection
- · Research and Development
- · Power Monitoring

Description

The L-com PPMDI-P48-191 is a Polarized Maintaining Dual Stage Isolator offered in Grade P (Premium). The wavelength is 1480nm with a cabling of 900um diameter and FC/APC, narrow key connectors. The L-com PPMDI-P48-191 features a packaging of 5.5X35mm and fiber length of 1M. The L-com PPMDI-P48-191 is one of thousands of fiber optic products in stock and ready to ship. Contact our knowledgeable technical support and sales staff with your questions on fiber optic connectivity or other L-com products.

Configuration

Polish APC
Module Function Isolator

Fiber Type PM Panda 900um Loose

Fiber Type
Fiber Type
Fiber Type
Fiber Type
Fiber Type
Fiber Type
900um
Package
5.5x35mm
Stage
Dual Stage
Grade
Grade P

Filter Specifications

Description	Minimum	Typical	Maximum	Units
Operating Bandwidth		20		nm
Extinction Ratio	20			dB
Insertion Loss		0.6	0.7	dB
Return Loss	55			dB
Isolation	45	55		dB
Optical Power			300	mW
Tensile Load			5	N

Size

Length 2.16 in [54.86 mm]
Weight 0.25 lbs [113.4 g]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Passive PM Dual Stage Isolator, Grade P, 1480nm, 1M 900um loose tube, FC/APC, narrow key PPMDI-P48-191



Passive PM Dual Stage Isolator, Grade P, 1480nm, 1M 900um loose tube, FC/APC, narrow key



PPMDI-P48-191

Environmental Specifications
Temperature
Operating Range
Storage Range

-5 to +70 deg C -40 to +85 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Passive PM Dual Stage Isolator, Grade P, 1480nm, 1M 900um loose tube, FC/APC, narrow key from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

PPMDI-P48-191 CAD Drawing

