

USB Cable Selection Guide

L-com offers a large variety of USB cables. The following matrix is intended to assist you in selecting the right cable for your application.

Connector / Cable Type & Features	USB 2.0 A Male	USB 2.0 Latching A Male	USB 2.0 B Male	USB 2.0 Mini B5 Female	USB 3.0 A Male	5 Position Female 0.100" Header Connector	Wire Leads / Cut End
USB 2.0 A Male	CSUZAA LSZH CSMUAA Premium		CSMUAB Premium ECUSBAB Deluxe CSUZAB LSZH WPUSBAB IP67 & Panel Mount WPUSBABSH IP67 & Panel Mount CAFLEX AM-BM Rotating/Flex CAUCLKAB Black Deluxe				
USB 2.0 A Female	CSMUAX Premium ECF504-xxAAS Panel Mount UPMAA Panel Mount CSMUAXMT-2M Panel Mount WPUSBAX IP67 & Panel Mount WPUSBAXSH IP67 & Panel Mount CAFLEX-AM-AF Rotating/Flex		UPMAB Panel Mount			UPMA5 Panel Mount	ECF504-5M Panel Mount WPUSBAF IP67 & Panel Mount
USB 2.0 Latching A Male		CAUALAL Latching CAUZALAL LSZH Latching	CAUALB Latching A COILUAB Coil CAUZALB LSZH Latching				
USB 2.0 B Male	CSMUAB Premium ECUSBAB Deluxe CSUZAB LSZH WPUSBAB IP67 WPUSBABSH IP67 CAFLEX AM-BM Rotating/Flex CAUCLKAB Black Deluxe	COILUAB Coil CAUALB Latching A	WPUSBBB IP67				
USB 2.0 B Female	WPUSBBA IP67 & Panel Mount UPMBA Panel Mount		UPMBB Panel Mount ECF504-xxBBS Panel Mount			UPMB5 Panel Mount	WPUSBBF IP67 & Panel Mount ECF504-B-5M Panel Mount
USB 2.0 Mini B5 Male	CSMUAMB5 Mini CAFLEX AM-MB5 Rotating/Flex CAFLEX MB5M-AM Rotating/Flex			CSMUMB5X Mini Extension COILMB5EXT Coil WPUSBMB5X IP67 & Panel Mount			
USB 2.0 Mini B4 Male	CSMUAMB4 Mini						
USB 2.0 Micro B Male	CSMUAMICB Mini						
USB 3.0 A Male					CAU3AA USB 3.0		
USB 3.0 A Female					CAU3AX USB 3.0		
USB 3.0 B Male					CAU3AB USB 3.0		
USB 3.0 Micro B Male					CAU3AMICB USB 3.0		