



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 11706 UPDATED DRAWING	03/04/2022	SRAUTUS


DESCRIPTION	MATERIAL	FINISH
BODY	BRASS	NICKEL PLATED
CENTER PIN	BRASS	GOLD PLATED
FERRULE	BRASS	NICKEL PLATED
INSULATOR	PTFE	NATURAL




FERRULE



CENTER PIN
(SOLDER TYPE)



BODY




NOTES:

ELECTRICAL:
 IMPEDANCE: 50 OHMS
 FREQUENCY RANGE: DC~6 GHz
 VOLTAGE RATING: 1500 VOLTS PEAK
 DIELECTRIC WITHSTANDING VOLTAGE: 2500 VOLTS RMS


PACKAGING:
 COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

MISCELLANEOUS:
 CABLE RETENTION: 80 LBS. PULL.
 APPLICATION: LMR6600, AND EQUIVALENT.
 ALL DIMENSIONS ARE FOR REFERENCE ONLY.



REGULATORY COMPLIANCE:
 EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)



RECOMMENDED
CABLE STRIPPING



RECOMMENDED
FERRULE CRIMP

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS .XX = ± .02 [5] ± 1/32 .XXX = ± .005 [13] ANGLES ± 1°	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY DFRISIELLO	04/28/2010	
	CHECKED BY	04/28/2010	
	APPROVED BY	04/28/2010	
THIRD-ANGLE PROJECTION	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION	CATEGORY COAXIAL CON, N-FEMALE CRIMP LMR600
	COLOR VARIATIONS MAY OCCUR	SIZE A	
CAGE CODE 43321	ITEM NO. ANF-1610	REV. E	
SCALE: NONE		CAD FILE: ANF-1610.SLDDRW	SHEET 1 OF 1