



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
B	ECN 5012: REMODELED, REDRAWN AND NEW FORMAT	09/03/2010	D.FRISIELLO
C	ECN 5802: CHANGED FREQUENCY RANGE TO 0 ~ 4GHz	10/31/2011	D.FRISIELLO
D	ECN 8213: UPDATE KNURL STYLE FROM STRAIGHT TO DIAMOND	12/16/2015	S.LI
E	ECN 11866: UPDATE MODELS AND DIMS	06/07/2022	SRAUTUS


DESCRIPTION	MATERIAL	FINISH
CONNECTOR BODY	BRASS	NICKEL PLATE
CONTACT	BRASS	GOLD PLATE
DIELECTRIC	PTFE	-
FERRULE	BRASS	NICKEL PLATE




FERRULE




CONTACT  
(SOLDER OR  
CRIMP .068" [1.72])



CONNECTOR BODY



RECOMMENDED  
FERRULE CRIMP SIZE



RECOMMENDED  
CABLE STRIPPING

NOTES:

ELECTRICAL:  
 IMPEDANCE: 50 OHMS  
 FREQUENCY RANGE: 0 ~ 4 GHz  
 VOLTAGE RATING: 500 VOLTS PEAK.  
 DIELECTRIC WITHSTANDING VOLTAGE: 1500 VOLTS RMS.  
 CABLE RETENTION: 30 LBS PULL

APPLICATION: 195-SERIES, RG58

COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  DIMENSIONAL TOLERANCES: .X = ±.1 [2.54] .XX = ±.01 [.25] .XXX = ±.005 [.13]  ANGULAR TOLERANCES: ALL = ± 1°  THIRD-ANGLE PROJECTION 	APPROVALS DRAWN BY DFRISIELLO	DATE 09/03/2010	 an INFINIT® brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936		
	CHECKED BY K.BURGNER	09/03/2010		CATEGORY COAXIAL	
	APPROVED BY K.BURGNER	09/03/2010	PRODUCT DESCRIPTION REVERSED POLARIZED TNC JACK		
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	CAGE CODE <b>43321</b>	DWG. NO. <b>ARTJ-1708</b>
SCALE: NONE		CAD FILE: ARTJ-1708.SLDDRW		SHEET 1 OF 1	