





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	3/1/05	PJP
B	ECN 5220: CREATE MODEL, NEW DRAWING FORMAT	2/7/11	D.FRISIELLO

DESCRIPTION	MATERIAL	FINISH
BODY	BRASS	NICKEL PLATE
PIN	BRASS	GOLD PLATE
DIELECTRIC	TEFLON	-
SHELL	BRASS	NICKEL PLATE
RETAINING RING	BRASS	NICKEL PLATE
GASKET	RUBBER	-



1/4-36UNS-2B
BOTH ENDS



NOTES:

IMPEDANCE: 50 OHM
 FREQUENCY RANGE: 0 ~6 GHz
 INSERTION LOSS: .15 dB MAX.
 VOLTAGE RATING: 500 VRMS MAX.
 DIELECTRIC WITHSTANDING VOLTAGE: 1000 Vrms MIN.

COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

ALL DIMENSIONS ARE FOR REFERENCE ONLY.

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY J.C.	3/1/05	
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005	CHECKED BY P.PESA	3/1/05	CATEGORY
	APPROVED BY P.PESA	3/1/05	COAXIAL
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION	
COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. AXA-RSPRSP
	SCALE: NONE	CAD FILE: AXA-RSPRSP.SLDDRW	SHEET 1 OF 1