







THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
C	ECN 5056: REDRAWN TO NEW SUPPLIER SPEC	9/30/10	D. CASTRO
D	ECN 5759: REDRAWN TO NEW SUPPLIER SPEC., NEW STRIP DIMS	10/6/11	D. FRISIELLO
E	ECN8062 FERRULE CRIMP .178 TO .133, PIN CRIMP .068 TO .074	08/20/15	B. PUCHASKI
F	ECN 8494 UPDATE ALL SPECS PER VENDOR	10/04/16	B. PUCHASKI

DESCRIPTION	MATERIAL	FINISH
BODY	BRASS	NICKEL 50μ INCH MIN.
DIELECTRIC	DELRIN	---
INNER CONTACT	BRASS	NICKEL 50μ INCH MIN. GOLD 2μ INCH MAX.
PLASTIC TUBE	DELRIN	---
FERRULE	BRASS	NICKEL 50μ INCH MIN.
WATERPROOF SEAL	PVC	ORANGE
WASHER	STEEL	NICKEL 50μ INCH MIN.
NUT	BRASS	NICKEL 50μ INCH MIN.



NOTES:

ELECTRICAL:
 IMPEDANCE: 50 OHMS.
 FREQUENCY: 0 - 11 GHz.
 VOLTAGE RATING: ≥ 500 V RMS
 INSULATOR RESISTANCE: ≥ 5G OHM
 DIELECTRIC WITHSTANDING VOLTAGE: 1500 V RMS
 CONTACT RESISTANCE: CENTER CONTACT ≤ 1.5 m OHM
 OUTER CONTACT ≤ 1 m OHM

PACKAGING:
 CONNECTOR SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
 CE2011/65/EU(RoHS DIRECTIVE)

RECOMMENDED
 PANEL CUTOUT

RECOMMENDED CABLE STRIPPING

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] DIMENSIONAL TOLERANCES: .X = ±.1 [2.54] .XX = ±.01 [25] .XXX = ±.005 [13] ANGULAR TOLERANCES: ALL = ± 1°	APPROVALS	DATE	50 HIGH STREET NORTH ANDOVER, MA 01845		
	DRAWN BY R. POLUBINSKI	8/6/07			CATEGORY
	CHECKED BY J. ROBERTS	8/17/10	PRODUCT DESCRIPTION	CONN TNC F BHD RG174 CRIMP	
	APPROVED BY ENG	8/17/10	SIZE	FSCM NO.	DWG. NO.
PROJECTION	COLOR VARIATIONS MAY OCCUR	A	43321	BAC528	
		SCALE: NONE	CAD FILE: BAC528.SLDDRW	SHEET 1 OF 1	