


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC.. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 7285: REVISED 3D MODEL AND DIMENSIONS, FORMAT, ROHS	2/7/14	D.FRISIELLO
F	ECN 7291: REVISE DIMENSION TO VENDOR SPEC., REVISED PACKAGING	2/11/14	D.FRISIELLO

DESCRIPTION	MATERIAL	FINISH
BODY	BRASS	NICKEL PLATE
CONTACT PIN	PHOSOROUS BRONZE	GOLD PLATE
INSULATOR BODY	ABS	NATURAL
GASKET	RUBBER	RED
WASHER	STEEL	NICKEL PLATE
NUT	BRASS	NICKEL PLATE



NOTES:

1. IMPEDANCE: 50 ohm
2. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
3. ADAPTER SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [51] .XXX = ±.005 [1.27]	APPROVALS DRAWN BY C.MCCORMICK CHECKED BY ENG APPROVED BY R.CARRICK	DATE 09/28/2001 09/28/2001 09/28/2001	L-com Global Connectivity 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY COAXIAL
	PROJECTION 		PRODUCT DESCRIPTION ADAPTER TNC F/TNC F BHD
	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321

SCALE: NONE CAD FILE: BA1090.SLDDRW SHEET 1 OF 1