


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/12/10	D.GRIFFIN



NMO 3/4" HOLE CRIMP CONNECTOR

TYPE-N MALE STRAIGHT CRIMP CONNECTOR

LENGTH CODE CHART		
CABLE# & LENGTH	LENGTH SYMBOL	EXAMPLES OF PART# USED
CA-AM1NMAXXX	WHERE XXX = LENGTH IN FEET	CA-AM1NMA010 (10 FEET)
CA-AM1NMANXX	WHERE NXX = LENGTH IN INCHES	CA-AM1NMA16 (16 INCHES)
CA-AM1NMAMXX	WHERE MXX = LENGTH IN METERS	CA-AM1NMAM07 (7 METERS)
CA-AM1NMAXMX	WHERE XMX = LENGTH IN DECIMAL METERS	CA-AM1NMA3M5 (3.5 METERS)

NOTES:

CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.

CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = $\pm .2$.XX = $\pm .02$.XXX = $\pm .005$	APPROVALS DRAWN BY D.FRISIELLO CHECKED BY K.BURGNER APPROVED BY K.BURGNER	DATE 11/12/10 11/12/10 11/12/10	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	CATEGORY COAXIAL	
PROJECTION 	SIZE A	FSCM NO. 43321	DWG. NO. CA-AM1NMA
SCALE: NONE		CAD FILE: CA-AM1NMA.SLDDRW	SHEET 1 OF 1