





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	RELEASED FOR PRODUCTION	01/12/06	MCCORMICK
B	ECN2935: PROD DESC WAS "50 OHM BNC F RG6 CRIMP"	08/08/07	R.POLUBINSKI
C	ECN 3165: UPDATE DWG FORMAT	1/21/08	D.GRIFFIN
D	ECN 4534: REVISED TITLE AND NEW FORMAT	2/2/10	D.FRISIELLO

DESCRIPTION	MATERIAL	FINISH
BODY	BRASS	NICKEL PLATE
FERRULE	BRASS OR COPPER ALLOY	NICKEL PLATE
PIN	BRASS	GOLD PLATE
INSULATOR	ACETAL	-



NOTES:  
 IMPEDANCE: 75 OHM  
 APPLICATION: RG6  
 COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATIONS PS-0031.  
 ALL DIMENSIONS ARE FOR REFERENCE ONLY.

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  DIMENSIONAL TOLERANCES: .X = ±.1 .XX = ±.02 .XXX = ±.005  ANGULAR TOLERANCES: ALL = ± 1°	APPROVALS C.MCCORMICK	DATE 01/12/2006			45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	CHECKED BY D.PARHAM	01/12/2006	CATEGORY COAXIAL		
	APPROVED BY M.LAHEY	01/12/2006	PRODUCT DESCRIPTION 75 OHM BNC F RG6 CRIMP		
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>BAC516</b>	REV. <b>D</b>
PROJECTION 	COLOR VARIATIONS MAY OCCUR		SCALE: NONE	CAD FILE: BAC516.SLDDRW	SHEET 1 OF 1