



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

DESCRIPTION	MATERIAL	FINISH
BODY	BRASS	NICKEL
CONTACT PIN	BRASS	GOLD
FERRULE	BRASS	NICKEL
INSULATOR	PTFE	-
GASKET	MVQ	-

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	3/20/09	D.GRIFFIN
B	ECN 4126: ADDED MATING/UNMATING TORQUES	7/14/09	D.FRISIELLO
C	ECN 4642: REVISED MATING TORQUE AND PACKAGING NOTE	3/25/10	D.FRISIELLO
D	ECN 10388: UPT DIM'S FOR PIN, FERRULE AND CABLE STRIPPING. ADD MATL CHART	09/28/2021	S.RAUTUS




NOTES:

IMPEDANCE: 50 OHM
 APPLICATION: RG223/U
 RECOMMENDED HEX CRIMP TOOL SIZE: .213 IN [5.41mm] & .068 IN [1.72mm].
 MATING TORQUE: .53 - 2.21 IN LBS [.06 - .25 Nm]

ALL DIMENSIONS ARE FOR REFERENCE ONLY.

COMPONENT ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
 EU ROHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936		
	DRAWN BY D.FRISIELLO	3/18/09		CATEGORY COAXIAL	
	CHECKED BY D.CASTRO	3/18/09			
APPROVED BY D.DOLCE	3/18/09	PRODUCT DESCRIPTION BNC, MALE, STRAIGHT, RG223/U			
THIRD-ANGLE PROJECTION	COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321	DWG. NO. BAC547	REV. D
		SCALE: NONE	CAD FILE: BAC547.SLDDRW		SHEET 1 OF 1