


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS |                 |          |           |
|-----------|-----------------|----------|-----------|
| REV       | DESCRIPTION     | DATE     | APPROVED  |
| A         | INITIAL RELEASE | 12/29/10 | D.GRIFFIN |
|           |                 |          |           |
|           |                 |          |           |





| LENGTH CODE CHART |                                      |                            |
|-------------------|--------------------------------------|----------------------------|
| CABLE# & LENGTH   | LENGTH SYMBOL                        | EXAMPLES OF PART# USED     |
| CA-FMEPBMAXXX     | WHERE XXX = LENGTH IN FEET           | CA-FMEPBMA010 (10 FEET)    |
| CA-FMEPBMANXX     | WHERE NXX = LENGTH IN INCHES         | CA-FMEPBMAN16 (16 INCHES)  |
| CA-FMEPBAMXX      | WHERE MXX = LENGTH IN METERS         | CA-FMEPBAM07 (7 METERS)    |
| CA-FMEPBMAXMX     | WHERE XMX = LENGTH IN DECIMAL METERS | CA-FMEPBMA3M5 (3.5 METERS) |

**RoHS Compliant** ✓

**NOTES:**

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL RECEIVE INSERTION LOSS TEST PER L-COM SPECIFICATIONS
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

|   |  |                            |  |
|---|--|----------------------------|--|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]<br>OVERALL CABLE LENGTH TOLERANCE:<br>≤12 [305] = +1 [25] / -0<br>>12 [305] ≤60 [1524] = +2 [51] / -0<br>>60 [1524] ≤120 [3048] = +4 [102] / -0<br>>120 [3048] ≤300 [7620] = +6 [152] / -0<br>>300 [7620] = +3% / -0% | APPROVALS  | DATE                       |  45 BEECHWOOD DRIVE<br>NORTH ANDOVER, MA<br>01845     |
|   | DRAWN BY<br>D. PARHAM                                    | 12/29/2010                 |  |
| ALL OTHER DIMENSIONAL TOLERANCES:<br>.X = ±.2<br>.XX = ±.02<br>.XXX = ±.005   | CHECKED BY<br>D. CASTRO                                  | 12/29/2010                 | CATEGORY<br><b>COAXIAL</b>   |
|   | APPROVED BY<br>K. BURGNER                                | 12/29/2010                 | PRODUCT DESCRIPTION<br><b>CA,CA-195 FME P/BNC MALE</b>   |
| PROJECTION<br>   | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY | COLOR VARIATIONS MAY OCCUR | SIZE <b>A</b> FSCM NO. <b>43321</b> DWG. NO. <b>CA-FMEPBMA</b> REV. <b>A</b><br>SCALE: NONE    CAD FILE: CA-FMEPBMA.SLDDRW    SHEET 1 OF 1 |