


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	2/24/16	D.GRIFFIN





LENGTH CODE CHART		
CABLE# & LENGTH	LENGTH SYMBOL	EXAMPLES OF PART# USED
CA-NMNMP1 \underline{XXX}	WHERE XXX = LENGTH IN FEET	CA-NMNMP1010 (10 FEET)
CA-NMNMP1 \underline{NXX}	WHERE NXX = LENGTH IN INCHES	CA-NMNMP1N16 (16 INCHES)
CA-NMNMP1 \underline{MXX}	WHERE MXX = LENGTH IN METERS	CA-NMNMP1M07 (7 METERS)
CA-NMNMP1 \underline{XMX}	WHERE XMX = LENGTH IN DECIMAL METERS	CA-NMNMP13M5 (3.5 METERS)

NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL RECEIVE INSERTION LOSS TEST PER L-COM SPECIFICATIONS.
3. CABLE ASSEMBLY COMPONENTS MEET ≤ -160 dBc
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY B.PUCHASKI	02/23/16	
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [1.51] .XXX = ±.005 [1.13]	CHECKED BY K.BURGNER	02/23/16	CATEGORY COAXIAL
	APPROVED BY P.PESA	02/23/16	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION CA-RG401 NM - NM LOW PIM	
COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. CA-NMNMP1
SCALE: NONE		CAD FILE: CA-NMNMP1.SLDDRW	REV. A
SHEET 1 OF 1			