


Coaxial Cable Specification

Specification		C734	Construction DWG.
Construction Item		Component	
Inner Conductor	Diameter	.032" [.81]	
	Material	20AWG SOLID SILVER PLATED COPPER	
Dielectric	Diameter	.150" [3.81]	
	Material	FPE	
Braid Shield	Material	80% BRAIDED TINNED COPPER	Marking On Surface
Foil Shield	Material	ALUMINUM FOIL 100%	
Jacket	Diameter	.236" [6]	
	Material	PVC	
	Color	GRAY	
Electrical/Environmental Characteristics			
Capacitance (Pf/m)		17.3	
Impedance (ohm)		75Ω	
Velocity (%)		80	
Max. Oper. Voltage (Vrms)		300V RMS	
Operating Temp. (°C)		-40°C TO+75°C	
Min. Bending Radius (mm)		2.5" [63.5]	
Listings/Ratings: CMR (UL) REGULATORY COMPLIANCE: CE2011/65/EU(RoHS DIRECTIVE)			

MODEL	PRIMARY PACKAGING	SECONDARY PACKAGING	LENGTH
C734-100	COIL	BOX	100 FT.
C734-500	SPOOL	STRETCH WRAP	500 FT.
C734-1K	SPOOL	STRETCH WRAP	1,000 FT.

(Information subject to change without notice)