


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/01/17	J.LABOY



LENGTH CODE CHART		
CABLE# & LENGTH	LENGTH SYMBOL	EXAMPLES OF PART# USED
CA-AMNFC $\underline{\text{XXX}}$	WHERE XXX = LENGTH IN FEET	CA-AMNFC010 (10 FEET)
CA-AMNFCN $\underline{\text{NXX}}$	WHERE NXX = LENGTH IN INCHES	CA-AMNFCN16 (16 INCHES)
CA-AMNFCM $\underline{\text{MXX}}$	WHERE MXX = LENGTH IN METERS	CA-AMNFCM07 (7 METERS)
CA-AMNFCX $\underline{\text{MX}}$	WHERE MXM = LENGTH IN DECIMAL METERS	CA-AMNFC3M5 (3.5 METERS)

NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL RECEIVE INSERTION LOSS TEST PER L-COM SPECIFICATIONS.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = $\pm .2$ [5.08] .XX = $\pm .02$ [5.1] .XXX = $\pm .005$ [1.3]	APPROVALS DRAWN BY B.PUCHASKI	DATE 11/01/17		50 HIGH STREET NORTH ANDOVER, MA 01845		
	CHECKED BY D.FRISIELLO	11/01/17		CATEGORY COAXIAL		
	APPROVED BY S.ELLIS	11/01/17	PRODUCT DESCRIPTION CA, CA100 ALPROX/NF			
	PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. CA-AMNFC
SCALE: NONE			CAD FILE: CA-AMNFC.SLDDRW		SHEET 1 OF 1	