


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	10/10/11	D.GRIFFIN



LENGTH CODE CHART		
CABLE# AND LENGTH	LENGTH SYMBOL	EXAMPLES OF PART# USED
CA-RTPNME \underline{XXX}	W HERE \underline{XXX} = LENGTH IN FEET	CA-RTPNME010 (10 FEET)
CA-RTPNMEN \underline{XX}	W HERE \underline{NXX} = LENGTH IN INCHES	CA-RTPNMEN16 (16 INCHES)
CA-RTPNMEM \underline{MXX}	W HERE \underline{MXX} = LENGTH IN METERS	CA-RTPNMEM07 (7 METERS)
CA-RTPNME \underline{XMX}	W HERE \underline{XMX} = LENGTH IN DECIMAL METERS	CA-RTPNME3M5 (3.5 METERS)

RoHS Compliant ✓

NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL RECEIVE INSERTION LOSS TEST PER L-COM SPECIFICATIONS.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D. CASTRO	10/6/11		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	CHECKED BY D. PARHAM	10/6/11	CATEGORY COAXIAL	
	APPROVED BY K. BURGNER	10/6/11	PRODUCT DESCRIPTION CA,CA-200 RP-TNC P / NM	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
			DWG. NO. CA-RTPNME	REV. A
			SCALE: NONE	CAD FILE: CA-RTPNME.SLDDRW
			SHEET 1 OF 1	