


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	7/23/10	D.GRIFFIN
B	ECN 5573: CN RELEASE, ADDED NOTE 2	6/29/11	D.FRISIELLO



LENGTH CODE CHART		
CABLE# & LENGTH	LENGTH SYMBOL	EXAMPLES OF PART# USED
CA-SMRNFA $\underline{XXX}$	WHERE XXX = LENGTH IN FEET	CA-SMRNFA010 (10 FEET)
CA-SMRNFAN $\underline{XX}$	WHERE NXX = LENGTH IN INCHES	CA-SMRNFAN16 (16 INCHES)
CA-SMRNFAM $\underline{XX}$	WHERE MXX = LENGTH IN METERS	CA-SMRNFAM07 (7 METERS)
CA-SMRNFA $\underline{XMX}$	WHERE XMX = LENGTH IN DECIMAL METERS	CA-SMRNFA3M5 (3.5 METERS)

RoHS Compliant ✓

NOTES:

- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL RECEIVE INSERTION LOSS TEST PER L-COM SPECIFICATIONS.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D. CASTRO	7/22/10		CATEGORY <b>COAXIAL</b>
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	CHECKED BY D. PARHAM	7/22/10	PRODUCT DESCRIPTION <b>CA, CA-195 SMA M RA/NF</b>	
PROJECTION 	APPROVED BY K. BURGNER	7/22/10		
	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>CA-SMRNFA</b>	REV. <b>B</b>
	SCALE: NONE		CAD FILE: CA-SMRNFA.SLDDRW	SHEET 1 OF 1