



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	1/31/14	D.GRIFFIN



PART NUMBER	LENGTH	
	METERS	FEET
CABLK90LA-LB-03M	0.3	.98
CABLK90LA-LB-05M	0.5	1.64
CABLK90LA-LB-1M	1.0	3.28
CABLK90LA-LB-2M	2.0	6.56
CABLK90LA-LB-3M	3.0	9.84
CABLK90LA-LB-5M	5.0	16.41

- NOTES:**
1. CABLE ASSEMBLY SHALL HAVE 360° SHIELD TERMINATION.
 2. CABLE ASSEMBLY SHALL MEET USB 2.0 REQUIREMENTS.
 3. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 > 12 [305] ≤ 60 [1524] = +2 [51] / -0 > 60 [1524] ≤ 120 [3048] = +4 [102] / -0 > 120 [3048] ≤ 300 [7620] = +6 [152] / -0 > 300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ± .005 [1.3]	APPROVALS DRAWN BY D.FRISIELLO CHECKED BY R.SCOTT APPROVED BY S. SMITH	DATE 1/31/14 1/31/14 1/31/14	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY USB
	PROJECTION 	COLOR VARIATIONS MAY OCCUR	PRODUCT DESCRIPTION CA USB 90LA A/90LA B BLK

FSCM NO.	DWG. NO.	REV.
43321	CABLK90LA-LB	A
SCALE: NONE	CAD FILE: CABLK90LA-LB.SLDDRW	SHEET 1 OF 1