




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	5/17/10	D.GRIFFIN
B	ECN 7065: REVISED LOGO'S, ADDED ROHS/CE NOTE	9/17/13	D.FRISIELLO
C	ECN 9040:UPDATE TO NEW LOGO PER SUPPLIER REQUEST,NEW DWG FORMAT	01/09/2018	B.ZHANG
D	ECN 10558: UPDATE DRAWING PER NEW VENDOR SPEC.	06/28/2020	B.GATES



7 POSITION SATA JACK



7 POSITION SATA PLUG



WIRING DIAGRAM

PART NUMBER	LENGTH	
	INCHES	mm
CASATAEXT-12	12.0	304.8
CASATAEXT-20	20.0	508.0

**NOTES:**

- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.  
INSULATION RESISTANCE: 10M ohms@300VDC  
CONDUCTIVE RESISTANCE: 5 ohms
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPEC. PS-0031.
- BOTH SHIELDS AND ALL DRAIN WIRES TIED TOGETHER.

**REGULATORY COMPLIANCE:**  
CE2011/65/EU(ROHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]      FRACTIONS ± 1/32 .XX = ± .02 [5]      ANGLES ± 1° .XXX = ± .005 [13]	APPROVALS DRAWN BY D. PARHAM CHECKED BY M. MARTINEZ APPROVED BY S. SMITH	DATE 05/12/10  05/12/2010  05/17/2010	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY  COLOR VARIATIONS MAY OCCUR	CATEGORY <b>HETEROGENOUS</b>  PRODUCT DESCRIPTION <b>CBL, SERIAL ATA EXTENSION</b>
SIZE <b>A</b> CAGE CODE <b>43321</b> DWG. NO. <b>CASATAEXT</b>		REV. <b>D</b>	