


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
B	ECN 11800 ADD BLACK HEATSHRINK	04/19/2022	SRAUTUS





LENGTH CODE CHART		
CABLE# & LENGTH	LENGTH SYMBOL	EXAMPLES OF PART# USED
CC-NMRSMA XXX	WHERE XXX = LENGTH IN FEET	CC-NMRSMA010 (10 FEET)
CC-NMRSMA NXX	WHERE NXX = LENGTH IN INCHES	CC-NMRSMA16 (16 INCHES)
CC-NMRSMA MXX	WHERE MXX = LENGTH IN METERS	CC-NMRSMA07 (7 METERS)
CC-NMRSMA XXM	WHERE XXM = LENGTH IN DECIMAL METERS	CC-NMRSMA3M5 (3.5 METERS)

NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL RECEIVE INSERTION LOSS TEST PER L-COM SPECIFICATIONS.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 > 12 [305] ≤ 60 [1524] = +2 [51] / -0 > 60 [1524] ≤ 120 [3048] = +4 [102] / -0 > 120 [3048] ≤ 300 [7620] = +6 [152] / -0 > 300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: $.X = \pm .2$ [5] FRACTIONS $\pm 1/32$ $.XX = \pm .02$ [.5] ANGLES $\pm 1^\circ$ $.XXX = \pm .005$ [.13]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936		
	DRAWN BY DCASTRO	03/19/2010		CATEGORY COAXIAL	
	CHECKED BY CBRAN	03/19/2010	PRODUCT DESCRIPTION CA,CA195 NM RA/SMA M		
	APPROVED BY KBURGNER	03/19/2010			CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR
THIRD-ANGLE PROJECTION 		SIZE A	CAGE CODE 43321	ITEM NO. CA-NMRSMA	REV. B
SCALE: NONE		CAD FILE: CA-NMRSMA.SLDDRW		SHEET 1 OF 1	