


8 7 6 5 4 3 2 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	6/4/10	D.GRIFFIN
B	ECN 5373: REVISED CABLE JACKET TO BLACK THERMOPLASTIC ELASTOMER	3/9/11	D.FRISIELLO



LENGTH CODE CHART		
CABLE# & LENGTH	LENGTH SYMBOL	EXAMPLES OF PART# USED
CA-NMRSPHXXX	WHERE XXX = LENGTH IN FEET	CA-NMRSPH010 (10 FEET)
CA-NMRSPHNXX	WHERE NXX = LENGTH IN INCHES	CA-NMRSPHN16 (16 INCHES)
CA-NMRSPHMXX	WHERE MXX = LENGTH IN METERS	CA-NMRSPHM07 (7 METERS)
CA-NMRSPHXXM	WHERE XM = LENGTH IN DECIMAL METERS	CA-NMRSPH3M5 (3.5 METERS)

RoHS Compliant ✓

NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D. PARHAM	06/02/2010		CATEGORY COAXIAL PRODUCTS
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	CHECKED BY C. BRAN	06/03/2010	PRODUCT DESCRIPTION CA,NM/RP-SMA P CA-400UF	
PROJECTION 	APPROVED BY K. BURGNER	06/03/2010		
	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. CA-NMRSPH
		SCALE: NONE	CAD FILE: CA-NMRSPH.SLDDRW	REV. B
				SHEET 1 OF 1