


8 7 6 5 4 3 2 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	6/3/10	D.GRIFFIN
B	ECN 5373: REVISED CABLE JACKET TO BLACK THERMOPLASTIC ELASTOMER	3/9/11	D.FRISIELLO



LENGTH CODE CHART		
CABLE# & LENGTH	LENGTH SYMBOL	EXAMPLES OF PART# USED
CA-NMRTPH $\underline{XXX}$	WHERE XXX = LENGTH IN FEET	CA-NMRTPH010 (10 FEET)
CA-NMRTPH $\underline{NXX}$	WHERE NXX = LENGTH IN INCHES	CA-NMRTPHN16 (16 INCHES)
CA-NMRTPH $\underline{MXX}$	WHERE MXX = LENGTH IN METERS	CA-NMRTPHM07 (7 METERS)
CA-NMRTPH $\underline{XMX}$	WHERE XMX = LENGTH IN DECIMAL METERS	CA-NMRTPH3M5 (3.5 METERS)

RoHS Compliant ✓

NOTES:

CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.

CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: $\leq 12$ [305] = +1 [25] / -0 $>12$ [305] $\leq 60$ [1524] = +2 [51] / -0 $>60$ [1524] $\leq 120$ [3048] = +4 [102] / -0 $>120$ [3048] $\leq 300$ [7620] = +6 [152] / -0 $>300$ [7620] = +3% / -0%	APPROVALS DRAWN BY D.FRISIELLO CHECKED BY K.BURGNER APPROVED BY K.BURGNER	DATE 6/3/10 6/3/10 6/3/10	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>
		DWG. NO. CA-NMRTPH	REV. <b>B</b>
		SCALE: NONE	CAD FILE: CA-NMRTPH.SLDDRW
		SHEET 1 OF 1	