


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE-COURTESY COPY TO CUSTOMER	3/29/10	D.GRIFFIN



LENGTH CODE CHART		
CABLE# & LENGTH	LENGTH SYMBOL	EXAMPLES OF PART# USED
CA-QPRQJBAXXX	WHERE XXX = LENGTH IN FEET	CA-QPRQJBA010 (10 FEET)
CA-QPRQJBANXX	WHERE NXX = LENGTH IN INCHES	CA-QPRQJBAN16 (16 INCHES)
CA-QPRQJBAMXX	WHERE MXX = LENGTH IN METERS	CA-QPRQJBAM07 (7 METERS)
CA-QPRQJBAXMX	WHERE MXM = LENGTH IN DECIMAL METERS	CA-QPRQJBA3M5 (3.5 METERS)

**RoHS Compliant** ✓

NOTES:  
 CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.  
 CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D.FRISIELLO	3/26/10		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	APPROVED BY K.BURGNER	3/26/10	CATEGORY <b>COAXIAL</b>	
	PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION <b>CA, 195 QMA RA P/QMA J BKHD</b>	
COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>CA-QPRQJBA</b>	REV. <b>A</b>
SCALE: NONE		CAD FILE: CA-QPRQJBA.SLDDRW		SHEET 1 OF 1