


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 3249: UPDATE DWG FORMAT	3/25/08	D.GRIFFIN
F	ECN 3312: CHANGE KIT P/N 1AB13-002 TO 1AB13-005	5/2/08	D.GRIFFIN
F	ECN 99999: ROTATED BNC COAX BOOT 180 DEG. NEW FORMAT	5/25/09	D.FRISIELLO
G	ECN 6469: UPDATED PACKAGING, LOGOS, ADDED ROHS STAMP	10/17/12	D. DESJARDIN





MODEL P/N	LENGTH FT [M]
CC59A-BF-1	1.0 [.30]
CC59A-BF-3	3.0 [.91]
CC59A-BF-6	6.0 [1.83]
CC59A-BF-9	9.0 [2.74]
CC59A-BF-12	12.0 [3.66]

NOTES:

1. CABLE SHALL BE TESTED FOR CONTINUITY.

 2. CABLE SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: $\leq 12$ [305] = +1 [25] / -0 $>12$ [305] $\leq 60$ [1524] = +2 [51] / -0 $>60$ [1524] $\leq 120$ [3048] = +4 [102] / -0 $>120$ [3048] $\leq 300$ [7620] = +6 [152] / -0 $>300$ [7620] = +3% / -0%  ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	APPROVALS DRAWN BY MCCORMICK CHECKED BY D.PARHAM APPROVED BY ENG	DATE 06/28/01 07/02/01 07/02/01	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY  COLOR VARIATIONS MAY OCCUR	CATEGORY COAXIAL		PRODUCT DESCRIPTION CA TYPE F PLUG/BNC M RG59A/U
PROJECTION 	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>CC59A-BF</b>	REV. <b>G</b>
SCALE: NONE		CAD FILE: CC59A-BF.SLDDRW		SHEET 1 OF 1