


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	RELEASED FOR PRODUCTION	05/14/01	MCCORMICK
B	REVISED TABLE ECN# 1128	06/24/02	MCCORMICK
C	PRODUCT VALIDATION UPDATES [ECN 1204]	10/29/02	P.LECLAIR
D	ECN 3288: UPDATE DWG FORMAT	4/28/08	D.GRIFFIN



MODEL #	LENGTH	
	FEET	METERS
CCSC188A-1	1.0	0.30
CCSC188A-1.5	1.5	0.46
CCSC188A-2	2.0	0.61
CCSC188A-2.5	2.5	0.76
CCSC188A-3	3.0	0.91
CCSC188A-4	4.0	1.22
CCSC188A-5	5.0	1.52
CCSC188A-7.5	7.5	2.29
CCSC188A-10	10.0	3.05

**NOTES:**

CABLE ASSEMBLY IS DESIGNED FOR HIGH TEMPERATURE APPLICATIONS (165°C)  
 CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY  
 CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN A POLYBAG

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  OVERALL CABLE LENGTH TOLERANCE: $\leq 12$ [305] = +1 [25] / -0 $>12$ [305] $\leq 60$ [1524] = -2[51] / -0 $>60$ [1524] $\leq 120$ [3048] = +4 / -0 $>120$ [3048] $\leq 300$ [7620] = +6 / -0 $>300$ [7620] = +5% / -0%  ALL OTHER DIMENSIONAL TOLERANCES: .X = .3 .XX = .15  PROJECTION 	APPROVALS DRAWN BY MCCORMICK CHECKED BY D.PARHAM APPROVED BY R.CARRICK	DATE 05/08/01 05/14/01 05/14/01	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845  CATEGORY COAXIAL	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION CA SMC M/SMC M RG188A/U	
	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. CCSC188A
	SCALE: NONE		CAD FILE: CCSC188A.SLDDRW	REV. <b>D</b>  SHEET 1 OF 1