


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	6/30/10	D.GRIFFIN



WIRE MAP		
"P1"	"P2"	COLOR
CENTER CONTACT	CENTER CONTACT	HIGH (+) BLUE WIRE
CYLINDRICAL CONTACT	CYLINDRICAL CONTACT	LOW (-) WHITE WIRE
CONNECTOR BODY	CONNECTOR BODY	CABLE SHIELD

LENGTH CODE CHART		
CABLE# & LENGTH	LENGTH SYMBOL	EXAMPLES OF PART# USED
CA-TRBP-PXXX	WHERE XXX = LENGTH IN FEET	CA-TRBP-P010 (10 FEET)
CA-TRBP-PNXX	WHERE NXX = LENGTH IN INCHES	CA-TRBP-P16 (16 INCHES)
CA-TRBP-PMXX	WHERE MXX = LENGTH IN METERS	CA-TRBP-PM07 (7 METERS)
CA-TRBP-PXXM	WHERE XMX = LENGTH IN DECIMAL METERS	CA-TRBP-P3M5 (3.5 METERS)

NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPEC. PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005	APPROVALS DRAWN BY D. CASTRO CHECKED BY K. BURGNER APPROVED BY K. BURGNER	DATE 6/30/10 6/30/10 6/30/10	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	CATEGORY COAXIAL PRODUCT DESCRIPTION CA,M17/176-00002 TRB P/P		
PROJECTION 	SIZE A	FSCM NO. 43321	DWG. NO. CA-TRBP-P	REV. A
SCALE: NONE		CAD FILE: CA-TRBP-P.SLDDRW		SHEET 1 OF 1