


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	5/6/13	D.GRIFFIN





LENGTH CODE CHART		
CABLE# & LENGTH	LENGTH SYMBOL	EXAMPLES OF PART# USED
CA4RNPRNPXXX	WHERE XXX = LENGTH IN FEET	CA4RNPRNP010 (10 FEET)
CA4RNPRNP $\underline{\text{NXX}}$	WHERE NXX = LENGTH IN INCHES	CA4RNPRNP16 (16 INCHES)
CA4RNPRNP $\underline{\text{MXX}}$	WHERE MXX = LENGTH IN METERS	CA4RNPRNPM07 (7 METERS)
CA4RNPRNP $\underline{\text{XMX}}$	WHERE XMX = LENGTH IN DECIMAL METERS	CA4RNPRNP3M5 (3.5 METERS)

NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL RECEIVE INSERTION LOSS TEST PER L-COM SPECIFICATIONS.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**RoHS Compliant** ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY B.PUCHASKI	05/03/13	
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	CHECKED BY P.PESA	05/03/13	CATEGORY <b>COAXIAL</b>
	APPROVED BY P.PESA	05/03/13	PRODUCT DESCRIPTION <b>CA400 RNP-RNP</b>
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b> FSCM NO. <b>43321</b> DWG. NO. <b>CA4RNPRNP</b> REV. <b>A</b>
SCALE: NONE		CAD FILE: CA4RNPRNP.SLDDRW	SHEET 1 OF 1