


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	RELEASED FOR PRODUCTION	05/21/01	MCCORMICK
B	PRODUCT VALIDATION UPDATES (ECN 1204)	10/29/02	P LECLAIR
C	ECN 3307: UPDATE DWG FORMAT	5/1/08	D.GRIFFIN



MODEL #	LENGTH	
	FEET	METERS
CCSR188A-1	1.0	0.30
CCSR188A-1.5	1.5	0.46
CCSR188A-2	2.0	0.61
CCSR188A-2.5	2.5	0.76
CCSR188A-3	3.0	0.91
CCSR188A-4	4.0	1.22
CCSR188A-5	5.0	1.52
CCSR188A-7.5	7.5	2.29
CCSR188A-10	10.0	3.05

**NOTES:**

CABLE ASSEMBLY IS DESIGNED FOR HIGH TEMPERATURE APPLICATIONS (165°C)  
CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY  
INDIVIDUALLY PACKAGE IN A POLYBAG

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  OVERALL CABLE LENGTH TOLERANCE: $\leq 12$ [305] = +1 [25] / -0 $>12$ [305] $\leq 60$ [1524] = -2[51] / -0 $>60$ [1524] $\leq 120$ [3048] = +4 / -0 $>120$ [3048] $\leq 300$ [7620] = +6 / -0 $>300$ [7620] = +5% / -0%  ALL OTHER DIMENSIONAL TOLERANCES: .X = .3 .XX = .15	APPROVALS DRAWN BY MCCORMICK	DATE 05/08/01		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CHECKED BY D.PARHAM	DATE 05/09/01		CATEGORY COAXIAL	
	APPROVED BY R.CARRICK	DATE 05/18/01	PRODUCT DESCRIPTION CA SMA M RA/SMA M RA RG188		
	PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. CCSR188A