


8 7 6 5 4 3 2 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	DRAWING REPLACES "CIB24MT2-OD1"	6/23/14	D. DESJARDIN



NOTES:

- CONNECTORS MOUNTED ON PRINTED CIRCUIT BOARD. TRACES CONNECT ALL LIKE-NUMBERED PINS ON ALL CONNECTORS.
- 200 MA. MAXIMUM CURRENT THROUGH ANY PIN.
- COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATIONS.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [1.51] .XXX = ±.005 [1.13]	APPROVALS T. CLARK CHECKED BY D. PARHAM APPROVED BY C. McCORMICK	DATE 10/16/2001 10/16/2001 10/16/2001	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			CATEGORY RACK/ENCLOSURES
	PROJECTION 	COLOR VARIATIONS MAY OCCUR CIB24MT2-OD1	SIZE A	FSCM NO. 43321 DWG. NO. CIB24MT2
	PRODUCT DESCRIPTION BUS STRIP, GPIB 8 GANG		SCALE: NONE CAD FILE: CIB24MT2.SLDDRW	REV. A SHEET 1 OF 1