


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	DRAWING REPLACES CIF24-03M-OD1	8/23/12	D.FRISIELLO
B	ECN 81 17: CORRECTED FUNCTION NAMES IN WIRE MAP.	10/1/15	D. DESJARDIN
C	ECN 10639: REMOVED RoHS STATEMENT	08/21/2020	PNEWTON



**SPECIFICATIONS:**

MEETS REQUIREMENTS OF ANSI/IEEE STD 488.1-1987.

**MATERIALS:**

CABLE: U.L. STYLE 2464, TWELVE TWISTED PAIRS 26AWG STRANDED COPPER, FOUR DATA PAIRS WITHIN ALUMINIZED POLYESTER FOIL SHIELD WITH DRAIN WIRE, PLUS EIGHT CONTROL PAIRS. OVERALL DOUBLE SHIELD ALUMINIZED POLYESTER FOIL PLUS BRAIDED COPPER SHIELD WITH DRAIN WIRE, GRAY PVC JACKET.  
 CONNECTOR HOUSINGS: DIE-CAST ALUMINUM ALLOY, NICKEL PLATED.  
 CONNECTOR INSULATORS: GLASS-FILLED PBT (BLUE), UL94V-0  
 CONNECTOR CONTACTS: COPPER ALLOY, 30 MICROINCHES GOLD OVER NICKEL  
 CONNECTOR SHELL: DIE-CAST ALLOY, NICKEL PLATED  
 THUMBSCREWS: STEEL, BLACK OXIDE FINISH



**ENVIRONMENTAL:**

OPERATING TEMPERATURE RANGE: -20°C TO + 80°C

**MISCELLANEOUS:**


SEE SHEET 2 FOR WIRE MAP  
 CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.  
 CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

MODEL NUMBER	LENGTH METERS [FEET]
CIF24-03M	0.33 [1.08]
CIF24-05M	0.50 [1.64]
CIF24-1M	1.0 [3.28]
CIF24-2M	2.0 [6.56]
CIF24-3M	3.0 [9.84]
CIF24-4M	4.0 [13.12]
CIF24-5M	5.0 [16.40]
CIF24-6M	6.0 [19.68]
CIF24-8M	8.0 [26.24]

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]   FRACTIONS ± 1/32 .XX = ± .02 [5]   ANGLES ± 1° .XXX = ± .005 [13]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	DRAWN BY TJC	8/17/01		CATEGORY <b>IEEE-488</b>
	CHECKED BY CM	8/22/01		
	APPROVED BY RC	9/10/01		
THIRD-ANGLE PROJECTION	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION	<b>DELUXE IEEE-488 CABLE ASSEMBLY</b>	
	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>   CAGE CODE <b>43321</b>   ITEM NO. <b>CIF24-03M</b>	REV. <b>C</b>	
		SCALE: NONE   CAD FILE: CIF24-03M.SLDDRW	SHEET 1 OF 2	

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

WIRING MAP			
PAIR NUMBER	J1/P1	J2/P2	FUNCTON
DATA GROUP IN INNER SHIELD			
1	1	1	DATA LINE DI01
	14	14	DATA LINE DI06
2	2	2	DATA LINE DI02
	3	3	DATA LINE DI03
3	4	4	DATA LINE DI04
	13	13	DATA LINE DI05
4	15	15	DATA LINE DI07
	16	16	DATA LINE DI08
CONTROL GROUP BETWEEN INNER AND OVERALL SHIELDS			
5	5	5	EOI
	24	24	EOI RETURN
6	6	6	DAV
	18	18	DAV RETURN
7	7	7	NRFD
	19	19	NRDF RETURN
8	8	8	NDAC
	20	20	NDAC RETURN
9	9	9	IFC
	21	21	IFC RETURN
10	10	10	SRQ
	22	22	SRQ RETURN
11	11	11	ATN
	23	23	ATN RETURN
12	17	17	REN
	24	24	REN RETURN
INNER SHIELD	24	24	INNER SHIELD
OVERALL SHIELD	12 & SHELL	12 & SHELL	OVERALL SHIELD

		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
CATEGORY			
IEEE-488			
PRODUCT DESCRIPTION			
DELUXE IEEE-488 CABLE ASSEMBLY			
SIZE	CAGE CODE	ITEM NO.	REV.
<b>A</b>	<b>43321</b>	CIF24	<b>C</b>
SCALE: NONE		CAD FILE: CIF24-03M.SLDDRW	SHEET 2 OF 2