


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	07/06/2023	SREITER	GUTTADAURO



CONNECTOR 1 CONNECTOR 2 MDR26 MALE CONNECTOR SDR26 MALE CONNECTOR

PIN 1	RED	PIN 1
PIN 14	GND1	PIN 14
PIN 2	BLACK	PIN 25
PIN 15	PINK	PIN 12
PIN 3	PINK	PIN 24
PIN 16	WHITE	PIN 11
PIN 4	BLUE	PIN 23
PIN 17	BLACK	PIN 10
PIN 5	WHITE	PIN 22
PIN 18	BROWN	PIN 9
PIN 6	BLACK	PIN 21
PIN 19	ORANGE	PIN 8
PIN 7	GREEN	PIN 20
PIN 20	WHITE	PIN 7
PIN 8	GREEN	PIN 19
PIN 21	BLACK	PIN 6
PIN 9	WHITE	PIN 18
PIN 22	ORANGE	PIN 5
PIN 10	BLACK	PIN 17
PIN 23	BROWN	PIN 4
PIN 11	BLUE	PIN 16
PIN 24	WHITE	PIN 3
PIN 12	WHITE	PIN 15
PIN 25	BLACK	PIN 2
PIN 13	GND(2)	PIN 13
PIN 26	BLACK	PIN 26
SHELL	BRAID	SHELL

PART NO.	LENGTH	
	FEET	METERS
CLCA05-3M	9.8	3
CLCA05-5M	16.4	5

NOTES:
 1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

REGULATORY COMPLIANCE:
 EU RoHS DIRECTIVE (MOST RECENTLY RELEASED VERSION).

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS SREITER	DATE 07/06/2023	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY SREITER	CHECKED BY DGUST	
THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	PRODUCT DESCRIPTION CAMERA LINK MACHINE VISION CABLE ASSEMBLY, MDR26 MALE PLUG TO SDR26 MALE PLUG, BLACK 29AWG CABLE
SIZE A		CAGE CODE 43321	ITEM NO. CLCA05
SCALE: NONE		CAD FILE: CLCA05-5M.SLDDRW	REV. A