



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	RELEASED FOR PRODUCTION	06/11/01	MCCORMICK
B	PRODUCT VALIDATION UPDATES [ECN 1204]	12/12/02	MCCORMICK
C	ECN 3282: UPDATE DWG FORMAT	4/14/08	D.GRIFFIN
D	ECN 8241: RELEASED TO SUZHOU, NEW FORMAT, UPDATE ROHS	2/2/16	S.LI



MODEL #	LENGTH	
	FEET	METERS
CCS58A-05HR	0.5	0.15
CCS58A-1HR	1.0	0.30
CCS58A-1.5HR	1.5	0.46
CCS58A-2HR	2.0	0.61
CCS58A-2.5HR	2.5	0.76
CCS58A-3HR	3.0	0.91
CCS58A-4HR	4.0	1.22
CCS58A-5HR	5.0	1.52
CCS58A-7.5HR	7.5	2.29
CCS58A-10HR	10.0	3.05



NOTES:

CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY INDIVIDUALLY PACKAGE IN A POLYBAG

REGULATORY COMPLIANCE:
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY MCCORMICK	06/06/01		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [51] .XXX = ±.005 [13]	CHECKED BY D.PARHAM	06/06/01	CATEGORY COAXIAL	
	APPROVED BY R.CARRICK	06/11/01	PRODUCT DESCRIPTION CA SMA M/SMA M RG58C/U	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
			DWG. NO. CCS58A-HR	REV. D
			SCALE: NONE	CAD FILE: CCS58A-HR.SLDDRW
				SHEET 1 OF 1