




8 7 6 5 4 3 2 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	CN INITIAL RELEASE	07/30/2013	B.Zhang
B	ECN8182; UPDT DWG FROM MOLDED THUMBSCREW TO METAL THUMBSCREW	11/28/2013	B.ZHANG

MODEL NUMBER	LENGTH	
	FEET	METERS
CTLDVIRAMT-3	3.0	[.92]
CTLDVIRAMT-5	5.0	[1.52]
CTLDVIRAMT-10	10.0	[3.05]
CTLDVIRAMT-15	15.0	[4.57]



UL STYLE 20276 CABLE(INNER,NOT SHOWN)
 (7) SHIELDED TWISTED PAIR, 28AWG, STRANDED TINNED COPPER,
 (1) UNSHIELDED TWISTED PAIR, 28AWG, STRANDED TINNED COPPER,
 SHIELDING(BRAIDED): 36AWG TINNED COPPER
 SHIELDING: ALUMINUM/POLYESTER
 OUTER JACKET: PVC; GRAY COLOR (PANTONE 424C)

PIN 8: NO CONNECTION

NOTES

1. METAL ARMOR CRUSH RESISTANCE: 1500PSI(MIN).
2. CABLE ASSEMBLY TO BE TESTED FOR CONTINUITY
3. CABLE ASSEMBLY TO BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPEC. PS-0031.
4. DUST COVERS INSTALLED FOR SHIPPING (NOT SHOWN).

REGULATORY COMPLIANCE:
 CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = $\pm .2$ [5.08] .XX = $\pm .02$ [51] .XXX = $\pm .005$ [13]	APPROVALS DRAWN BY B.Zhang	DATE 02/22/2013		50 HIGH STREET NORTH ANDOVER, MA 01845	
	CHECKED BY F.MAO	07/30/2013		CATEGORY AUDIO/AUDIO/VIDEO	
	APPROVED BY T.LU	07/30/2013	PRODUCT DESCRIPTION CBL, DVI-DDL M/R.A M W/METAL ARMOR	SIZE A	FSCM NO. 43321
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	DWG. NO. CTLDVIRAMT	REF	SCALE: NONE CAD FILE: CTLDVIRAMT.SLDDRW
	REF	SHEET 1 OF 1	REV. B		