


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 8577: REVISED CONNECTORS, FORMAT, RoHS STAMP, NOTES	12/2/16	D.FRISIELLO
F	ECN 8627: REVISED CONNECTORS TO NEW VENDOR SPECS	2/2/17	D.FRISIELLO





MODEL NUMBER	LENGTH	
	FEET	METERS
CCSB188A-1	1.0	0.30
CCSB188A-1.5	1.5	0.46
CCSB188A-2	2.0	0.61
CCSB188A-2.5	2.5	0.76
CCSB188A-3	3.0	0.91
CCSB188A-4	4.0	1.22
CCSB188A-5	5.0	1.52
CCSB188A-7.5	7.5	2.29
CCSB188A-10	10.0	3.05

**NOTES:**

- CABLE ASSEMBLY IS DESIGNED FOR HIGH TEMPERATURE APPLICATIONS (200 °C).
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE	 50 HIGH STREET NORTH ANDOVER, MA 01845				
	DRAWN BY MCCORMICK	05/08/01					
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ±.005 [1.13]	CHECKED BY D.PARHAM	05/14/01	CATEGORY COAXIAL				
	APPROVED BY R.CARRICK	05/14/01	PRODUCT DESCRIPTION CA SMB M/SMB M RG188A/U				
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	<table border="1"> <tr> <td>SIZE <b>A</b></td> <td>FSCM NO. <b>43321</b></td> <td>DWG. NO. <b>CCSB188A</b></td> <td>REV. <b>F</b></td> </tr> </table>	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>CCSB188A</b>	REV. <b>F</b>
SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>CCSB188A</b>	REV. <b>F</b>				
SCALE: NONE		CAD FILE: CCSB188A.SLDDRW	SHEET 1 OF 1				