


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 8627: REVISED CONNECTORS TO NEW VENDOR SPECS	02/02/2017	DFRISIELLO
F	ECN 9976: REVISED CABLE DESCRIPTION TO RG316	07/16/2019	SELLIS





MODEL NUMBER	LENGTH	
	FEET	METERS
CCSB316-1	1.0	0.30
CCSB316-1.5	1.5	0.46
CCSB316-2	2.0	0.61
CCSB316-2.5	2.5	0.76
CCSB316-3	3.0	0.91
CCSB316-4	4.0	1.22
CCSB316-5	5.0	1.52
CCSB316-7.5	7.5	2.29
CCSB316-10	10.0	3.05

NOTES:

CABLE ASSEMBLY IS DESIGNED FOR HIGH TEMPERATURE APPLICATIONS (200 °C).

CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.

CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE	 50 HIGH STREET NORTH ANDOVER, MA 01845	
	DRAWN BY MCCORMICK	05/08/2001		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [51] .XXX = ±.005 [1.13]	APPROVED BY R.CARRICK	05/14/2001	CATEGORY COAXIAL	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION CA SMB M/SMB M RG316/U		
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. CCSB316
		SCALE: NONE	CAD FILE: CCSB316.SLDDRW	SHEET 1 OF 1