


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	07/12/2012	DFRISIELLO
B	ECN 9400: REMOVE THE NOTE "CHANGEABLE INSERTS" FROM P2 END	09/03/2018	SLI



NOTES:

MATERIAL:

CONNECTORS
 SHELL: STEEL OR COPPER ALLOY
 INSULATOR: THERMOPLASTIC, UL94V-0
 CONTACTS: COPPER ALLOY
 COUPLER: BRASS WITH 80µ" MIN. LIGHT NICKEL PLATING
 ARMOR CABLE: STAINLESS STEEL.

FINISH:

SHELL: NICKEL PLATE
 CONTACTS: 30µin MIN GOLD PLATE, OVER NICKEL PLATE

CABLE CHARACTERISTICS:


UL STYLE 2725
 1X TWISTED PAIR 28AWG (7/0.127mm) STRANDED TINNED COPPER,
 2X 20 AWG (7/0.32mm) STRANDED TINNED COPPER,
 OVERALL ALUMINIZED POLYESTER SHIELD, STRANDED TINNED COPPER DRAIN WIRE,
 TINNED COPPER BRAID SHIELD, PVC JACKET, BLACK
 CABLE DIAMETER: .201 [5.1] REF.

MISCELLANEOUS:

METAL CRUSH RESISTANCE: 1500 PSI (MIN).
 CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
 CABLE ASSEMBLY SHALL HAVE 360° SHIELD TERMINATION.
 CONNECT DRAIN WIRE TO CONNECTOR SHELL.
 CABLE ASSEMBLY MUST MEET REQUIREMENTS OF USB 2.0

REGULATORY COMPLIANCE:

CE2011/65/EU (RoHS DIRECTIVE)



MODEL NO.	LENGTH METERS [FEET]
CSMUAB-MT-03M	0.3 [.98]
CSMUAB-MT-05M	0.5 [1.64]
CSMUAB-MT-1M	1.0 [3.28]
CSMUAB-MT-2M	2.0 [6.56]
CSMUAB-MT-3M	3.0 [9.84]
CSMUAB-MT-4M	4.0 [13.12]
CSMUAB-MT-5M	5.0 [16.41]

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [51] .XXX = ±.005 [1.27]	APPROVALS DRAWN BY DFRISIELLO CHECKED BY F.MAO APPROVED BY S.SMITH	DATE 10/11/2011 10/11/2011 10/11/2011	L-com Global Connectivity 50 HIGH STREET NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY USB	
	PROJECTION 		PRODUCT DESCRIPTION CA, USB A-M/B-M METAL ARMORED	
	COLOR VARIATIONS MAY OCCUR		SIZE A	FSCM NO. 43321