

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	3/5/14	D.GRIFFIN
-	-	-	-
-	-	-	-

(2X .463
[11.75]
MIN.)

LENGTH

ONE 28AWG STRANDED TINNED COPPER TWISTED PAIR
TWO 20AWG STRANDED TINNED COPPER CONDUCTORS
OVERALL ALUMINIZED POLYESTER SHIELD WITH DRAIN WIRE
PLUS TINNED COPPER BRAIDED SHIELD.
PVC OUTER JACKET, CLEAR


PIN 1
DIELECTRIC
2X SERIES "A"
USB PLUG
CONTACTS: 30 μINCHES
GOLD PLATING

"P1"

"P2"

2X MOLDED HOOD
AND STRAIN RELIEF,
PVC, CLEAR

"P1" WIRING DIAGRAM "P2"



MODEL NUMBER	LENGTH METERS [FEET]
CSMUCLRAA-03M	0.3 [.98]
CSMUCLRAA-05M	0.5 [1.64]
CSMUCLRAA-1M	1.0 [3.28]
CSMUCLRAA-2M	2.0 [6.56]
CSMUCLRAA-3M	3.0 [9.84]
CSMUCLRAA-5M	5.0 [16.40]

NOTES:

1. CABLE ASSEMBLY SHALL HAVE 360° SHIELD TERMINATION.
2. CABLE ASSEMBLY SHALL MEET USB 2.0 REQUIREMENTS.
3. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D. CASTRO	1/10/14		CATEGORY
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [51] .XXX = ±.005 [1.27]	CHECKED BY D. FRISIELLO	1/10/14	PRODUCT DESCRIPTION	
PROJECTION 	APPROVED BY S. SMITH	1/13/14	CA, USB CLEAR TYPE A/A	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE A	FSCM NO. 43321
	COLOR VARIATIONS MAY OCCUR		DWG. NO. CSMUCLRAA	REV. A
			SCALE: NONE	CAD FILE: CSMUCLRAA.SLDDRW
			SHEET 1 OF 1	