



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
B	ECN 4087: CN RELEASE	7/12/09	B. ZHANG
C	ECN 4168: ADDED L-COM LOGO BOTH SIDES	8/4/09	D. CASTRO
D	ECN 6638: UPDATED FORMAT, PACKAGING, AND LOGOS	1/31/13	D. DESJARDIN
E	ECN 8163: ADDED HIPOT TEST NOTE 3. UPD ROHS.	11/6/15	D. DESJARDIN



UL 20276
 (6) 30AWG COAXIAL LINES, BRAIDED SHIELD;
 (1) 28AWG TWISTED PAIR, AL/MYLAR SHIELD;
 (2) 30AWG TWISTED PAIR, AL/MYLAR SHIELD, W/DRAIN WIRE;
 (1) 28AWG TWISTED PAIR,
 (2) 30AWG TWISTED PAIR, AL/MYLAR SHIELD, W/DRAIN WIRE;
 (1) 24AWG TWISTED PAIR,
 (1) 24AWG TWISTED PAIR,
 (6) 28AWG SINGLE CONDUCTOR,
 OVERALL SHIELD: AL/MYLAR AND BRAID,
 OUTER JACKET: PVC, GRAY (PANTONE 424C)

MODEL NUMBER	LENGTH	
	FEET	METERS
CTLEVCMM-3	3.0	0.91
CTLEVCMM-5	5.0	1.52
CTLEVCMM-10	10.0	3.05
CTLEVCMM-15	15.0	4.57
CTLEVCMM-25	25.0	7.62
CTLEVCMM-50	50.0	15.24



NOTES:

1. PINS 8, 18 AND 28 RECESSED TO PROVIDE PROPER POWER/GROUND SEQUENCING
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL PASS 750VDC HIPOT TEST.
4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
 CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY B. ZHANG	05/22/09		CATEGORY AUDIO/VIDEO
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005	CHECKED BY F. MAO	06/12/09	PRODUCT DESCRIPTION CA VIDEO EVC M/EVC M	
	APPROVED BY F. MAO	06/12/09		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR SIZE A FSCM NO. 43321 DWG. NO. CTLEVCMM REV. E
PROJECTION 	REF	SCALE: NONE	CAD FILE: CTLEVCMM.SLDDRW	SHEET 1 OF 1