

8 7 6 5 4 3 2 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	02/26/2020	PHOSPODAR

FIBER TYPE	BREAKOUT SINGLEMODE, RISER
CORE DIAMETER	9 μm
CLADDING DIAMETER	125 μm
PRIMARY COATING DIA. (UV CURED ACRYLATE)	500 μm
SECONDARY BUFFER DIA. (HARD ELASTOMERIC)	900 μm
NUMERICAL APERTURE	0.20
PROOF TEST LEVEL	100 kpsi

WAVELENGTH:	1310 nm	1550 nm
MAXIMUM ATTENUATION	0.5 dB/km	
NOMINAL ZERO DISPERSION SLOPE	0.092 ps/(nm ² -km)	



CABLE WEIGHT	41 kg/km (28 lbs/1000 ft)
CABLE DIAMETER	7.0 mm (0.28 in)

INSTALLATION:	
MAX TENSILE LOAD	1200 N (270 lbs)
MIN BEND RADIUS	10.5 cm (4.1 in)

OPERATING:	
MAX TENSILE LOAD	500 N (110 lbs)
MIN BEND RADIUS	7 cm (2.8 in)



IMPACT RESISTANCE	1500 IMPACTS
CRUSH RESISTANCE	2200 N/cm

OPERATING TEMPERATURE	-40°C TO +85°C
STORAGE TEMPERATURE	-55°C TO +85°C
INSTALLATION TEMPERATURE	-10°C TO +60°C (actual temp. of cable)
FLAME RETARDANCY	OFNR



ALL DIMENSIONS IN mm, DRAWING NOT TO SCALE

NOTES:
1. CABLE SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (mm) OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [5] ANGLES ± 1° .XXX = ± .005 [13]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936		
	DRAWN BY DZINN	02/26/2020			
	CHECKED BY DFRISIELLO	02/26/2020	CATEGORY	FIBER OPTIC	
	APPROVED BY PHOSPODAR	02/26/2020	PRODUCT DESCRIPTION	1M Interval Single Mode (9/125) Low-Water-Peak	
THIRD-ANGLE PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321	ITEM NO. FOB25SNGRKB2-M	REV. A
		SCALE: NONE	CAD FILE: FOB25SNGRKB2-M.SLDDRW	SHEET 1 OF 1	