


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISION | | | | | |
|----------|-----|-----------------|------------|------------|-----------|
| ZONE | REV | DESCRIPTION | DATE | CHANGED BY | APPROVED |
| | A | INITIAL RELEASE | 08/25/2023 | KGLEBOVA | PHOSPODAR |



NOTES:

1. CONNECTOR SUPPLIED WITH A DUST CAP INSTALLED WHICH IS NOT SHOWN.
2. CONNECTOR COMES IN KIT OF SUB-COMPONENTS.
3. CONNECTOR SHALL BE INDIVIDUALLY PACKAGED IAW L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
EU ROHS DIRECTIVE (MOST RECENT RELEASED VERSION)

| | | | | | |
|---|--|-------------|---|----------------------------|--|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13] | APPROVALS | DATE | <div>L-com™</div> <div>an INFINITI® brand</div> | | 50 High Street, West Mill, North Andover, MA 01845 USA Phone: 1.800.341.5266 1.978.682.6936 |
| | DRAWN BY KGLEBOVA | 08/17/2023 | | | |
| | CHECKED BY DMAY | 08/17/2023 | CATEGORY | | |
| | APPROVED BY PHOSPODAR | 08/17/2023 | | FIBER OPTIC | |
| THIRD-ANGLE PROJECTION | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY | | PRODUCT DESCRIPTION CS CONNECTOR (2F), SINGLE MODE FIBER WITH APC POLISH, 2MM BOOT AND 55MM TAB LENGTH IN WHITE | | |
| | COLOR VARIATIONS MAY OCCUR | SIZE A | CAGE CODE 43321 | ITEM NO. FOC-CSSA62-55W | REV. A |
| | | SCALE: NONE | CAD FILE: FOC-CSSA62-55W.SLDDRW | | SHEET 1 OF 1 |