



6		5		4		3		2		1	
LENGTH				OPTICAL SPECIFICATION		REVISION					
LENGTH (L) METER [FEET]	TOLERANCE MM [INCHES]	FIBER TYPE	SINGLE MODE		ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED	
5 [16.40]	+50/-0 [+1.97/0]	CONNECTOR TYPE	IP-MPO/APC			B	ECO-13297	02/08/2024	DZINN	PHOSPODAR	
10 [32.81]	+100/-0 [+3.94/0]	INSERTION LOSS	≤ 0.75dB								
20 [65.62]	+1%*L/-0	RETURN LOSS	≥ 55dB								
30 [98.43]	+1%*L/-0	TEST WAVE LENGTH	1310 & 1550nm								



NOTES:

- MPO CONNECTOR ASSEMBLY POLISH TYPE: APC
- MPO POLARITY: TIA METHOD B.
- ALL CONNECTORS INCLUDE PROTECTIVE DUST CAPS.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IAW L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS		 an INFINIT@ brand Website: www.L-com.com Phone: 1.800.341.5266 1.978.682.6936		 INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5	
TOLERANCES: .X = ±.2 [5] .XX = ±.02 [0.5] .XXX = ±.005 [0.13]				FRACTIONS ± 1/32 ANGLES ± 1°	
CABLE LENGTH TOLERANCES: ≤12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0		DESCRIPTION IP68 OUTDOOR CABLE ASSY, 5MM OD, OS2, MPO/APC MALE 24F TO MPO/APC MALE 24F, TYPE B		SCALE NONE	SHEET 1 OF 1
SIZE A	CAGE CODE 43321	DRAWN BY DZINN	ITEM NO. FOCS20DMPMB24	REV B	